

# PolyCera® Hydro 100 Ultrafiltration Ultra-High Solids Spiral Monolith® Element Specifications

#### **Performance & Operating Parameters**

Membrane material:PolyCera HydroNominal Pore Size/MWCO:20 nm/100 kDa

Operating pH Ranges: 1.0 – 12.0

Operating Temperature Ranges: 5°C – 50°C (41°F – 122°F)

Maximum Inlet Pressure: 8.3 bar (120 psi)

Maximum Cross-Flow Per Element: 56.8 m³/h (250 gpm)

Max Pressure Drop Per Element:0.35 bar (5 psi)Feed Free Oil & Grease:≤ 5 mg/LFeed Total Suspended Solids:≤ 3000 mg/L

Continuous Free Chlorine:  $\leq$  5 mg/L Typical Operating Flux:  $\leq$  0 - 200 LMH (12 - 118 GFD)


Feed Spacer Thickness: 120 mil
Recommended Pre-Filter: 500 µm

Model Number Size	Hydro 100XB-1812- UHS-TWM 1812		Hydro 100XB-4040- UHS-TWM 4040		Hydro 100XB-8040- UHS-FRF 8040	
Active Area $m^2$ ( $ft^2$ )	0.11	(1.1)	2.5	(27)	11.1	(119)
Weight kg (lb)	0.45	(1)	3.5	(8)	13	(29)
Outer Wrap	Таре		Таре		Fiberglass	
Endcap	Male		Male		Female	
Recommend crossflow m³/h (gpm)	1.8	(8)	9.1	(40)	56.8	(250)
Filtrate flowrate* $m^3/h$ (gpm)	0.02	(0.1)	0.43	(1.9)	1.9	(8.4)
Permeate connection D-1** cm (in)	1.71	(0.67)	1.90	(0.75)	2.86	(1.13)
Element diameter D-2 cm (in)	4.6	(1.80)	10.2	(4.00)	20.3	(8.00)
Element length (Female) L-1 cm (in)	30.48	(12.00)	101.6	(40.00)	NA	
Element length (Male) L-1 cm (in)	29.8	(11.75)	96.1	(37.93)	101.6	(40.00)
Feed channel height H-1 mm (mil)	3.05	(120)	3.05	(120)	3.05	(120)

**Note**: \*Testing condition: deionized water, 25°C, 1.7 bar (25 psi) transmembrane pressure. Actual results will vary depending on feed water quality and operation conditions.

<sup>\*\*</sup>All element dimensions have specified tolerances of +0.00/-0.06"





## **Cleaning & Chemical Exposure Guidelines**

Maximum backwash pressure: 1.7 bar (25 psi)

Backwash flux: 40 - 240 LMH (24 - 144 GFD)

Standard backwash duration: 30 seconds

Maximum backwash duration: 2 minutes

Maximum cleaning temperature:  $50^{\circ}\text{C} (122^{\circ}\text{F}) @ 10 < \text{pH} \le 13.5,$ 

 $70^{\circ}$ C (158°F) @  $1 \le pH \le 10$ 

Maximum cleaning pH: 1.0 < pH < 13.5 @ 50°C (122°F),

1.0 < pH < 10.0 @70°C (158°F)

Hydrochloric acid:  $\leq$  0.4% or 1.0 Normal (pH > 1.0)

Citric acid:  $\leq$  20% or 1.0 Normal (pH > 1.0) Sodium hydroxide:  $\leq$  4% or 1.0 Normal (pH < 13.5)

Free chlorine instantaneous/total: 100 ppm/300,000 ppm hour @ pH 11

Peroxide/Ozone: Not compatible

Notes: 1) Increased crossflow during backwash enhances cleaning efficacy

2) Backwash flux should be 1.5 to 2 times of operating flux

#### **Handling & Storage Instructions**

## New Element Handling & Storage Guidelines

- ♦ Handle with care. Damage to elements/end-caps/ATDs can compromise performance
- ♦ It is recommended to store elements wet and horizontally
- ♦ Whenever possible, store elements in original packaging
- ♦ Drying can damage membrane surface and compromise performance
- ♦ Membrane elements should be stored in dry, dark, and ventilated conditions



#### **Installation & Initial Use Guidelines**

- ♦ Prior to use, soak element for 24 hours with DI water then flush for at least 30 minutes
- ♦ Elements can be mounted vertically or horizontally
- ♦ When mounted vertically, it is recommended to orient feed to flow from top to bottom
- ♦ Use water or glycerin to lubricate seal

### **After Use Storage & Preservation Guidelines**

Use standard CIP procedure to clean feed and filtrate from the elements prior to shut down. Then perform element preservation as recommended below:

- ↑ week to 6 months: Fill up element and housing with 0.3% Saniclean\* solution, seal the housing and store. Every two weeks drain the Saniclean solution from the system and flush with clean water. Refill the element and housing with 0.3% Saniclean solution, seal the housing and store.
- ♦ More than 6 months: Contact PolyCera, Inc. for further information.

**Note:** Saniclean is a USDA accepted, low-foaming acid anionic rinse product made by Five Star Chemicals & Supplies, Inc. (Colorado, USA). Please contact Five Star Chemicals & Supplies, Inc. or PolyCera, Inc. for further information.

PolyCera, Inc.

721 S Glasgow Ave., Unit D, Los Angeles, CA 90301 +1 424.331.7700 | info@polyceramembranes.com polyceramembranes.com