

PolyCera® Hydro 100 Ultrafiltration


Ultra-High Solids Spiral Monolith®

Performance & Operating Parameters		Cleaning & Chemical Exposure Guidelines	
Membrane Material:	PolyCera Hydro	Max Backwash Pressure:	1.7 bar (25 psi)
Nominal Pore Size/MWCO:	20 nm/100 kDa	Backwash Flux:	40 - 240 LMH (24 - 144 GFD)
Operating pH Range:	1.0 – 12.0	Standard Backwash Duration:	30 seconds
Operating Temperature Ranges:	5°C – 50°C (41°F – 122°F)	Max Backwash Duration:	2 minutes
Max Inlet Pressure:	8.3 bar (120 psi)	Max Cleaning Temperature:	50°C (122°F) @ 10 < pH ≤ 13.5, 70°C (158°F) @ 1 ≤ pH ≤ 10
Max Cross-Flow Per Element:	56.8 m³/h (250 gpm)		
Max Pressure Drop Per Element:	0.35 bar (5 psi)	Max Cleaning pH:	1.0 < pH < 13.5 @ 50°C (122°F), 1.0 < pH < 10.0 @ 70°C (158°F)
Max Free Oil & Grease:	≤ 5 mg/L		
Max Total Suspended Solids:	≤ 10,000 mg/L	Hydrochloric Acid:	≤ 0.4% or 1.0 Normal (pH > 1.0)
Typical Operating Flux:	20 - 200 LMH (12 - 118 GFD)	Citric Acid:	≤ 20% or 1.0 Normal (pH > 1.0)
Recommended Pre-Filter:	500 µm	Sodium Hydroxide:	≤ 4% or 1.0 Normal (pH < 13.5)
		Free Chlorine Instantaneous/Total:	100 ppm/300,000 ppm hour @ pH 11
		Peroxide/Ozone:	Not compatible
Notes: 1) Increased crossflow during backwash enhances cleaning efficacy 2) Backwash flux should be 1.5 to 2 times of operating flux			

Model Number	Hydro 100XB-1812-UHS-TWM	Hydro 100XB-4040-UHS-TWM	Hydro 100XB-8040-UHS-FRF
Size	1812	4040	8040
Active Area m² (ft²)	0.11 (1.1)	2.5 (27)	11.1 (119)
Weight kg (lb)	0.45 (1)	3.5 (8)	13 (29)
Outer Wrap	Tape	Tape/Fiberglass	Fiberglass
Endcap	Male	Male	Female
Recommend crossflow m³/h (gpm)	1.8 (8)	9.1 (40)	56.8 (250)
Filtrate flowrate* m³/h (gpm)	0.02 (0.1)	0.43 (1.9)	1.9 (8.4)
Permeate connection D-1** cm (in)	1.71 (0.67)	1.90 (0.75)	2.86 (1.125)
Element diameter D-2 cm (in)	4.6 (1.80)	10.2 (4.00)	20.3 (8.00)
Element length (male) L-1 cm (in)	30.48 (12.00)	101.6 (40.00)	NA
Element length (female) L-2 cm (in)	29.8 (11.75)	96.1 (37.93)	101.6 (40.00)
Feed channel height H-1 mm (mil)	3.05 (120)	3.05 (120)	3.05 (120)
Notes: *Testing condition: de-ionized water, 25°C, 1.7 bar (25 psi) transmembrane pressure. Actual results will vary depending on feed water quality and operation conditions. **All element dimensions have specified tolerances of +0.00/-0.06".			



ELEMENT SPECIFICATIONS



Handling & Storage Instructions

New Element Handling & Storage Guidelines

- Recommended storage temperature: 5°C – 20°C (41°F – 68°F). Do not freeze element.
- Handle with care. Damage to elements/end-caps/ATDs can compromise performance.
- It is recommended to store elements wet and horizontally.
- Whenever possible, store elements in original packaging.
- Drying can damage membrane surface and compromise performance.
- Membrane elements should be stored in dry, dark, and ventilated environmental conditions.

Installation & Initial Use Guidelines

- Prior to use, soak element for 24 hours with portable water then flush for at least 30 minutes.
- Elements can be mounted vertically or horizontally.
- When mounted vertically, it is recommended to orient feed to flow from top to bottom.
- Use water or glycerin to lubricate seal.

After Use Storage & Preservation Guidelines

Use standard CIP procedure to clean feed and filtrate from the elements prior to shut down. Then perform element preservation as recommended below:

- 1–7 days: Sanitize element by flushing with 10 ppm bleach and adjust to pH 11 for 30 minutes. Fill up element and housing with fresh 1 ppm bleach solution, seal the housing and store.
- 1 week to 6 months: Fill up element and housing with 0.3% Saniclean* solution, seal the housing and store. Every four weeks drain the Saniclean solution from the system and flush with clean water. Refill the element and housing with 0.3 % Saniclean solution, seal the housing and store. If Saniclean solution is not available, use 0.2% sodium azide solution or 45% glycerin solution instead.
- More than 6 months: Contact PolyCera, Inc. for further information.

*: Saniclean is a USDA accepted, low-foaming acid anionic rinse product made by Five Star Chemicals & Supplies, Inc. (Colorado, USA).

PolyCera, Inc.
721 S Glasgow Ave.
Unit D
Los Angeles, CA 90301

T +1.424.331.7700
W www.polyceramembranes.com
E info@polyceramembranes.com

© 2018 PolyCera, Inc. All rights reserved.

Hydro.100.120UHS.S.12.19